

ACCU-CAL™ 50-LED RADIOMETER

Consistent light curing requires periodic monitoring of light energy intensity and dosage levels. The ACCU-CAL™ 50-LED radiometer is simple to operate and offers accurate measurement of curing energy. The ACCU-CAL™ 50-LED can measure energy levels emitted from lightguides (3 mm, 5 mm, and 8 mm) and LED flood lamps. A spectral sensitivity range of 350 - 450 nm and intensity measurement from 1 mW/cm² to 40 W/cm², makes this unit ideal for measuring LED curing source energy levels. A specially designed photo-sensor assembly provides repeatable measurements and protection from high temperatures associated with some LED systems on the market.

Simple to Operate ■ Set Screw Locks Lightguide in Place ■ PTB and NIST Traceable



ACCU-CAL™ 50-LED for measuring flood lamps only. PN 40519



ACCU-CAL™ 50-LED for measuring LED spot lamps and flood lamps. PN 40505

Three Reasons to Use a Radiometer

- **Maintaining a Reliable Light-Curing Process** – A radiometer helps to ensure that a light-curing system is providing the intensity and dosage levels required for successful curing.
- **Providing a Worker-Friendly Light-Curing Process** – The ACCU-CAL™ 50-LED is sufficiently sensitive to measure the intensity of stray or reflected energy (as little as 1 mW/cm²). DYMAX recommends that worker UVA exposure not exceed 1 mW/cm². For reference, UV (320-395 nm) intensity on a sunny day can range from 2-6 mW/cm².
- **Measuring Transmission Rates Through Substrates** – A radiometer can be used to measure the transmission rates of various wavelengths through substrates that sometimes absorb various frequencies of energy. To assure an effective curing process it is critical to measure the light intensity reaching the cure site below any intervening substrate.

SPECIFICATIONS	
Spectral Sensitivity	350 to 450 nm
Intensity Range	1 mW/cm ² to 40 W/cm ²
Resolution	Intensity (1 mW/cm ² ; to three significant digits) Dose (1 mJ/cm ²)
Calibration Period	12 months
Operating Temperature Ranges	Optometer: +5 to +40°C Detector: 120°C continuous, Peak 200°C
Measurement Modes	Intensity (mW/cm ²) Peak Intensity (mW/cm ²) Dose (m J/cm ²)
Light Sources	Lightguides (3 mm, 5 mm, and 8 mm), LED Flood Lamps
Power Supply	Two (2) AA batteries
Battery Life	250 hours (automatic shutoff after 1 hour)
Sensor Dimensions	Photo-Sensor Diameter = 9 mm Diameter = 37 mm Thickness = 8 mm Cable Length = 1 M
Meter Dimensions	145 mm (Length) x 63 mm (Width) x 30 mm (Thickness)

RADIOMETERS and ACCESSORIES		
Product	Part #	Description
ACCU-CAL™ 50-LED for LED Spot and Flood Units	40505	Complete radiometer with lightguide adapters (3 mm, 5 mm, and 8 mm) and lightguide simulator*; includes storage/carrying case
ACCU-CAL™ 50-LED for LED Flood Units	40519	Complete radiometer for LED flood and conveyor systems; includes storage/carrying case
Flood to Spot Adapter Kit	39554	Kit includes three lightguide adapters (3 mm, 5 mm, and 8 mm) and a lightguide simulator*
3 mm Lightguide Adapter	39556	Fits 3 mm ID lightguides (5 mm OD)
5 mm Lightguide Adapter	39557	Fits 5 mm ID lightguides (7 mm OD)
8 mm Lightguide Adapter	39558	Fits 8 mm ID lightguides (10 mm OD)
Lightguide Simulator	38408	Lightguide simulator (Fits all standard lightguide entrance fittings)

*A lightguide simulator is used to measure direct spot lamp intensity (required to calculate lightguide transmission)

For further assistance with adhesive and equipment selection, contact DYMAX Applications Engineering.



In the U.S. Call: 877.396.2988
 In North and South America Call: +1.860.482.1010
 In Europe Call: +49 (0) 611.962.7900
 In China Call: +86.755.83485759
 In Asia Call: +852.2460.7038
 In Korea Call: 82.2.784.3434

www.dymax.com ♦ www.dymax.de ♦ www.dymax.com.cn ♦ www.dymax.co.kr

DYMAX Corporation - 318 Industrial Lane - Torrington, CT 06790 - Phone: 860.482.1010 - Fax: 860.496.0608 - E-mail: info@dymax.com - www.dymax.com

DYMAX Europe GmbH – Kasteler Strasse 45 – Building G 359 - 65203 Wiesbaden, Germany - Phone: +49 (0) 611.962.7900 - Fax: +49 (0) 611.962.9440 - E-mail: info_de@dymax.com - www.dymax.de

DYMAX UV Adhesives & Equipment (Shenzhen) Co., Ltd - Unit 807, Talfook Building, No. 9 Shihua Road, Futian Free Trade Zone, Shenzhen, China 518038 - Phone: +86.755.83485759 - Fax: +86.755.83485760 - E-mail: dymaxasia@dymax.com - www.dymax.com.cn

DYMAX Asia (HK) - Room 1103, 11/F., Metro Centre, Phase I, 32 Lam Hing St., Kowloon Bay, Hong Kong - Phone: +852.2460.7038 - Fax: +852.2460.7017 - E-mail: dymaxasia@dymax.com - www.dymax.com.cn

DYMAX Korea LLC - #903, CCMM B/D, 12 Yeoido-Dong, Youngdungpo-Gu, Seoul, Korea, 150-869 - Phone: 82.2.784.3434 - Fax: 82.2.784.5775 - E-mail: info@dymax.kr - www.dymax.co.kr

© 2009-2010 DYMAX Corporation. All rights reserved. All trademarks in this bulletin, except where noted, are the property of, or used under license by DYMAX Corporation, U.S.A.

The data contained in this bulletin is of a general nature and is based on laboratory test conditions. DYMAX Europe GmbH does not warrant the data contained in this bulletin. Any warranty applicable to products, its application and use is strictly limited to that contained in DYMAX Europe GmbH's General Terms and Conditions of Sale published on our homepage http://www.dymax.com/de/pdf/dymax_europe_general_terms_and_conditions_of_sale.pdf. DYMAX Europe GmbH does not assume any responsibility for test or performance results obtained by users. It is the user's responsibility to determine the suitability for the product application and purposes and the suitability for use in the user's intended manufacturing apparatus and methods. The user should adopt such precautions and use guidelines as may be reasonably advisable or necessary for the protection of property and persons. Nothing in this bulletin shall act as a representation that the product use or application will not infringe a patent owned by someone other than DYMAX Corporation or act as a grant of license under any DYMAX Corporation Patent. DYMAX Europe GmbH recommends that each user adequately test its proposed use and application of the products before actual repetitive use, using the data contained in this bulletin as a general guide. LIT276EU Rev 06/14/2010